

OM-102

Operating Microscope



Introduction

- OM Series Operating Microscopes using LED light source for coaxial illumination, have different working distance and magnification. They are featured for flexible handling and easy operation. They can be used for micro-operation in ear-nose-throat, dental, ophthalmology, gynecology, and surgery.
- OM-102 is mainly used for micro-operating in dental and ophthalmology surgery.

Technical Specifications

PARAMETER	SPECIFICATION
Observation Angle	45°tilted
Magnification of Observation	6X
Interpapillary Distance	50mm-80mm
Diopter	±5D
Focal Length of Objective	F=200mm and F=300mm two objectives
Magnification Changer	3-step: 0.6X, 1X, 1.6X
Total Magnification	3X, 5X, 8X, 4.7X, 7.5X, 12X
Linear Field	60.8mm, 37.9mm, 23.6mm, 40.6mm, 25.3mm, 15.8mm
Fine Focusing Distance	10mm
Illumination	Coaxial illumination with 10W LED lamp light source, brightness adjustable, illumination>30000lx

Lamp	10W LED lamp
Filter	Built-in green and orange filters
Balancing arm	2-part arm with universal joints
Floor stand	2-part column fitted on the five-star base with casters
Power supply input	AC100V-240V, 50-60HZ
Power supply adapter	DC12V3A, 36W
Optional Accessories	Beam splitter, Video camera adapter, Demonstrator, Camera (U3CMOS03100KPA, WUCAM0720PA, FHD2100, HD200), Monitor (S24R352FHC), Objective F=250mm & F=400mm, Wall mount bracket, Monitor mount (GM112B, DS312B)